

BASYS™

Any Application. Any Environment.™

Healthcare



Display guides caregiver through CDC recommended hand wash.

Available in multiple heights to fit any application in the healthcare environment.

Ideal for areas where handwashing compliance is a concern.

Provides self-guided instruction to improve hand hygiene.



SLOAN®

BASYS™

Any Application. Any Environment.™

Informed by in-depth research and backed by Sloan's century of experience and proven technologies, BASYS offers a modular platform of body types, features and components to meet the needs of any healthcare environment.



BASYS' Guided Handwash Improves Caregiver Hand Hygiene

WET		SCRUB		RINSE		DONE	

- Caregiver places hands under faucet and water flow begins. Display reads "H2O".
- Caregiver wets hands for 2 seconds.
- Display then reads "Soap". Caregiver removes hands to get soap.
- Caregiver scrubs with soap for a minimum of 15 seconds.
- Display then reads "H2O". Caregiver places hands under faucet to rinse.
- Caregiver rinses for a minimum of 5 continuous seconds.
- Display reads "PASS" to signify completion.
- Total wash time is displayed when hands are removed.

CDC compliant and non-compliant hand washes are saved in BASYS memory.

Other Key Features

- Line Purge
- Hardwired, Battery or Solar Powered
- Electronic override for continuous flow needs
- 4-inch and 8-inch base plates available

How to Order

EFX-XXX → Crown
 ↓ ↘ Power
 Body type

	High	Mid	Low	Low IB	Wall*
Hardwire	107	207	307	607	807
Battery	157	257	357	657	857
Solar	177	277	377	677	877

Handwashingforlife® Healthcare has endorsed the BASYS™ touch-free electronic faucet as a best practice in hand hygiene. The Handwashingforlife® endorsement is based on design features that lower the risk for cross contamination, reduce water consumption and improve the quality and frequency of caregiver hand hygiene.

BASYS™ displays the wash time and water temperature with every wash. Handwashingforlife® testing has shown this visual feature encourages more frequent washing and makes self-monitoring more reliable. The CDC reports the average wash time is an unacceptable 8-10 seconds. BASYS™ time monitoring overcomes the "short wash."

BASYS™ wash time feature is "selectable." The wash time can be set for specific locations or when C-Difficile and other outbreaks occur.

BASYS™ incorporates an automatic line purge. In low usage locations purging reduces the risk for legionella build up in water systems.

BASYS™ is eco-friendly. Reliable and consistent hand sensing technology delivers water only when needed saving up to a gallon of water with each hand wash.



*Wall Available 4Q13

For more in-depth specifications, or to build a BASYS™ faucet online, visit: sloanvalve.com/healthcare

SLNBH07/132.2K - B10017



World Headquarters:
 10500 Seymour Ave. Franklin Park, IL 60131
 T: 847.671.4300 / 800.9.VALVE.9
 F: 847.671.6944 / 800.447.8329

©2013 Sloan Valve Company. All rights reserved.

Legend: Hardwired Battery Solar Turbine

SLOAN®